




Latakas L-1,0 m
bė dugno nuolydis

| Latakas | | Sąrašas | | | |
|---------|--------|---------|----------|-------|-------|
| Modelis | Plotis | Spalva | Medžiaga | Medis | Medis |
| KL 5.01 | 200 | V1120 | Alu | 11200 | 11200 |
| KL 5.02 | 200 | V1120 | Alu | 11200 | 11200 |
| KL 5.03 | 150 | V1120 | Alu | 11200 | 11200 |
| KL 5.04 | 150 | V1120 | Alu | 11200 | 11200 |
| KL 5.05 | 200 | V1120 | Alu | 11200 | 11200 |




Latakas L-0,5 m
su ruošiniu vamzdiu Ø200;
su ruošiniu "L", "T" formos
linijai formuoti

| Latakas | | Sąrašas | | | |
|---------|--------|---------|----------|-------|-------|
| Modelis | Plotis | Spalva | Medžiaga | Medis | Medis |
| KL 5.11 | 200 | V1120 | Alu | 11200 | 11200 |
| KL 5.12 | 200 | V1120 | Alu | 11200 | 11200 |
| KL 5.13 | 150 | V1120 | Alu | 11200 | 11200 |
| KL 5.14 | 150 | V1120 | Alu | 11200 | 11200 |
| KL 5.15 | 200 | V1120 | Alu | 11200 | 11200 |




Įlekiamo dėžės su
nėsvarumų indu

| Latakas | | Sąrašas | | | |
|---------|--------|---------|----------|-------|-------|
| Modelis | Plotis | Spalva | Medžiaga | Medis | Medis |
| KL 5.16 | 200 | V1120 | Alu | 11200 | 11200 |
| KL 5.17 | 200 | V1120 | Alu | 11200 | 11200 |
| KL 5.18 | 150 | V1120 | Alu | 11200 | 11200 |
| KL 5.19 | 150 | V1120 | Alu | 11200 | 11200 |



Latakas L-0,5 m
su angeli tarpine vamzdiu Ø200;
su ruošiniu "L", "T" formos
linijai formuoti

| Latakas | | Sąrašas | | | |
|---------|--------|---------|----------|-------|-------|
| Modelis | Plotis | Spalva | Medžiaga | Medis | Medis |
| KL 5.20 | 200 | V1120 | Alu | 11200 | 11200 |
| KL 5.21 | 200 | V1120 | Alu | 11200 | 11200 |
| KL 5.22 | 150 | V1120 | Alu | 11200 | 11200 |
| KL 5.23 | 150 | V1120 | Alu | 11200 | 11200 |
| KL 5.24 | 200 | V1120 | Alu | 11200 | 11200 |



Multiline V200